## Vibrator Control RSP1

with Time addition

## RSP1

ZIEHL



Part numberr:

Z224305

ohne BR 1/2 $\longrightarrow$ kein Intervall-Rütteln BR1 $3 \longrightarrow 5$ mal BR2 $2 \longrightarrow 15$ mal $4 \longrightarrow 15$ mal 4	K1-0) K2-0) K3-7) S
T0 = Gesamtlaufzeit Absaugung T1 = Austrudelzeit T2 = Intervail - Rütteln T3 = Intervail - Pause T4 = Dauerrüttelzeit	4 - 120 min 10 - 300 sec 1 - 30 sec 1 - 30 sec 10 - 300 sec 1022 121

The vibration control RSP1 is a compact multiple timing relay for capturing operation times of suction plants and for triggering vibrators.

It provides optimal control of the vibration device by collecting of operating times of up to 3 suctions


- addition of the running time of 1, 2 or 3 suctions.
- introduction of vibration procedure after having reached the set total time (adjustable 4 to 120 min.) and after completion of the last suction operation.
- external vibration command by closing a contact, e.g. by filter monitoring work
- spintime adjustable 10 to 300 sec.
- interval vibrations 5, 15 or 20 times (disconnectable)
- interval vibration time (adjustable 1 - 30 sec.)
- interval break time (adjustable 1 - 30 sec.)
- continuous vibration (adjustable 10 - 300 sec.)
- no vibration during suction operation.
- if vibration procedure is interrupted (e.g. by switching on suction), the same will be recommenced at the next possible opportunity.

with variable programs for vibration procedures (spintime, interval- and permanent vibration) and programmable vibration periods. LED displays provide information about the operational state at any time.

All times are permanently saved in an EEPROM. Thus the accumulated operation period of the suction operation saved when switching off the supply voltage, e.g. during the night or weekend.

Features:

- inputs for up to 3 suctions.
- permanent saving of all times in the EEPROM.
- LED-display
- 2 pushbuttons for programming.
- coding switch for adjustment of all times
- RESET-button, resets operation period to zero or interrupts a running vibration procedure.
- VIBRATION-button, starts vibration procedure (only if suction is not active).



Technical Data

Supply voltage Us

Relay output Contact type Test Conditions max. ambient temperature

Inputs Contact 6, 7, 8 against 5 Contact 1 against 4

Casing dimensions (W x H x D) Protection housing/terminals Mounting

Weight

## AC 220 - 240 V, ± 10%, 50/ 60 Hz, < 3 VA

1 NO

**type 2** see "general technical informations" see "general technical informations" -20°C...+55°C

approx. DC 24 V/3 mA approx. DC 5 V/5 mA

Design S 12: 41.5 x 82 x 121 IP 30/ IP 20 on 35 mm standard rail according to EN 60 715 or with M4 screws. approx. 300 g

4